SERVOMEX 5200 MULTI PURPOSE

PORTABLE BENCHTOP GAS ANALYSER

For analysing the composition of common gas mixtures in laboratories and light industrial applications

- Non-depleting paramagnetic and infra-red measurement technology ensures the unit is always ready for use
- Accurate, reliable and component specific, giving confidence that observed values are credible and not due to background interference
- Customer pre-tested software offers ease of use, simple calibration and advanced features
- Innovative construction gives a robust unit with a space saving footprint
- Rechargeable battery and vehicle power (12/24V) options enable mobile use



SPECIFICATION

O₂ and/or CO₂ (CO to follow) **GASES MEASURED**

MEASUREMENT PERFORMANCE Technology:		OXYGEN Paramagnetic		CARBON DIOXIDE Infra-red
Variant:	Standard accuracy		High accuracy	All variants
Full scale range (FSR):	0-100% O ₂		0-100% O ₂	0-10% or 0-25% CO ₂
Minimum output range:	0-10% O ₂		0-1% O ₂	0-10% FSR
Accuracy, general use:	±0.2% O ₂		±0.05% O ₂	±2% FSR
Accuracy, stable environment:	±0.1% O ₂		±0.02% O ₂	±1% FSR
Zero drift, per week:	±0.4% O ₂		±0.2% O ₂	±4% FSR
Response time (T ₉₀):	<10 seconds		<15 seconds	<10 seconds
Tilt effect, at 15° from cal:	±0.3% O ₂		±0.15% O ₂	±1% FSR
Pressure effect:	Directly proportional to ambient barometric pressure		<0.2% reading / mBar change	

PHYSICAL

Operating temperature: -10°C to +50°C (+14°F to +122°F) 5°C to +45°C (+41°F to +113°F) Temp. coefficient, zero: ±0.2% O₂ per 10°C (18°F) ±1% FSR/10°C (18°F) ±5% FSR/ 10°C (18°F)

Temp. coefficient, span: ±0.3% O₂ per 10°C (18°F) W 150mm (6.0") x D 260mm (10.5") x H 300mm (12.0") Dimensions: Weight: 2.6kgs (5.7lbs) to 3.9kgs (8.6lbs) depending on configuration

SAMPLE

Sample gas: Clean, dry, non-flammable and non-toxic gases only Flow variation effect: $\pm 0.1\%$ O₂ for a $\pm 0.5\%$ psig (3.5kPa) change

±0.5% FSR for a 10psig (70kPa) change To maximise measurement stability, unpumped units are supplied with an automatic flow control device (AFCD). Flow control:

Over the specified inlet pressure range this controls sample flow rate to approximately 1.5 to 6 litres

(0.05 to 0.2 cubic feet) per minute

Inlet pressure: Without pump 7kPa (1psig) to 70kPa (10psig)

With optional internal pump -7kPa (-1psig) to 3.5kPa (0.5psig)

5mm OD stub with "Quickconnect" barb fitting for 6.3mm (¼") ID tube or adaptor to ½" NPT fitting option Sample inlet connection:

Sample outlet connection: 5mm OD stub (sample and bypass)

Replaceable 0.6µm glass fibre particulate filter Sample filter:

Response time - All at 10psig (70kPa)

Flow effect - AFCD version, within specified sample gas supply range



SERVOMEX 5200 MULTI PURPOSE

The Servomex 5200 Multi Purpose gas analyser has been specifically designed to meet the demanding needs of field and laboratory analysts, light industrial users and others who require fast, accurate and reliable analysis of common gas mixtures. This compact, portable and easy to use instrument is based upon a non-depleting, component specific measurement technique (magnetodynamic paramagnetic and infra-red) for long life and minimal running costs, avoiding the problems associated with electrochemical or other less robust methods of analysis.

The 5200 Multi Purpose replaces the well established Servomex 244, 404, 571, 572 and 575 analysers. Where there is no risk of an explosive atmosphere it may also be used to replace the Model 570.

APPLICATION EXAMPLES:

Physiology studies Universities Laboratory reactors Fermentation Medical gas verification

APPROVALS:

ORSAT validated to meet USFDA performance requirements for verifying medical oxygen USP and nitrogen NF. CE marked and in compliance with the EEC EMC and WEEE Directives.

UL, TÜV, FCC and PSE approved 100-240V AC power supply.

OPTIONS

Internal pump	0.8l (0.03 cu.ft)/min internal pump with user configurable timer		
	When an internal pump is specified users may also select sample outlet location front \square or rear \square		
Analogue output	One 4-20mA output per measurement. (Note RS 232 output included as standard on base model)		
Rechargeable batteries	Advanced lithium ion batteries providing 8-36 hours use, depending on sensor selections		
Vehicle power adaptor	Allows the unit to run/recharge from 12/24V DC vehicle socket		
Printer	Preformatted compact, mains power/rechargeable printer		
Additional barb fittings	Additional QuickConnect fittings to simplify connection of zero and span gases		
1/4" NPT adaptor	QuickConnect fitting to allow connection to hard pipes		
2 years spares	Recommended spares for two years operation, comprising replacement filters (5) and filter cap 'O' ring		

ADDITIONAL ACCESSORIES AVAILABLE (consult your local sales contact):

Flue Gas Conditioning Panel Flow Meters Sampling Probes Transport Case

NOTE: These analysers are not medical devices as defined in the Medical Devices Directive 93/42EEC and are not intended to be used on human beings for the diagnosis, prevention, monitoring, treatment or alleviation of disease, injury or replacement or modification of the anatomy.

www.servomex.com

SERVOMEX COMPANIES, AGENTS AND REPRESENTATIVES ARE LOCATED THROUGHOUT THE WORLD. YOUR NEAREST CONTACT IS:

Visit www.servomex.com for technical data sheets, application and technology information for all Servomex analysers.

Servomex has a policy of constant product improvement and therefore reserves the right to change specifications without notice.





(44) 1892 652181

(31) 79-346 42 42

Servomex Group Limited, Jarvis Brook, Crowborough, East Sussex, TN6 3DU, England Servomex B.V., Stephensonstraat 20, 2723 RN Zoetermeer, Netherlands Servomex S.A., 8 Rue Proudhon, B.P. 50, 93212 St Denis La Plaine Cedex, France

Servomex GmbH, Münsterstraße 5, 59065 Hamm, Germany

Servomex Company Inc., 525 Julie Rivers, Suite 185, Sugar Land, Texas 77478-2847, USA.

Servomex Asia Pacific Ltd, 7F, No.88, Sec. 6, Chung Shan N. Rd., Taipei, Taiwan

Servomex Group Limited., SAIF Zone, Executive Suites Z1-56, PO Box 8962, Sharjah, UAE. Servomex Asia Pacific Ltd. (Spectris Instrumentation and Systems (Shanghai) Ltd)

Building 9, Shanghai Euromate Industrial Park, No.88 Lane 2888 Hua Ning Road, Xingzhuang Industrial Park, Shanghai 201108 PR China

Servomex Japan, Spectris Co.Ltd., 1F JP Kaji-cho Bldg., 3-5-2 Kandakaji-cho, Chiyoda-ku,Tokyo 101-0045, Japan

Global email: info@servomex.com

(33) 1 49 46 22 50 Fax (33) 1 49 46 22 51 (49) 23 81 68 82 13 Fax (49) 23 81 68 81 75 (1) 281-295-5800 Fax (1) 281-295-5899

(1) 281-295-5800 Fax (1) 281-295-5899 (886) 2-2833 8848 Fax (886) 2-2833 8844 Fax (971) 6 557 0303 Fax (971) 6 557 1242

Fax

(44) 1892 662253

(31) 79-342 08 19